

### Specification


Door Operator	DS-75	DS-150	DS-75	DS-150
Opening Method	Bi-parting		Single sliding	
Applicable Door Mass x Door q'ty	75x2	100x2	75x1	100x1
Door area DW XDH (m <sup>2</sup> )	2.6			
Applicable Door Width:DW (mm)	762~1067			
Rate of DH/DW	3.0			
R from door center (mm)	1200R~			
Average speed	0.4m/s or less			
Maximum Operable Wind Speed	100VAC•5A			

### Notice

- 1, All drawings herein are subject to change without notice.
- 2, For further details, please contact NABCO sales distributors

Circular Sliding Door  
 Operation Unit "Eu"  
 Installation Drawing of  
 Access Panel inside type  
 (Elevation)  
 Scale 1:20

改訂No.	改訂日時
番号 No.	
1HP102561-01	
<b>Nabtesco</b> Nabtesco Corporation	



Notice

- 1, All drawings herein are subject to change without notice.
- 2, For further details, please contact NABCO sales distributors

Circular Sliding Door  
 Operation Unit "Eu"  
 Installation Drawing of  
 Access Panel inside type  
 (Section)  
 Scale 1:20

改訂No.	改訂日時
1HP102561-02	
<b>Nabtesco</b> Nabtesco Corporation	

参考図書