

### Specification

Door Operator	DS-75	DS-150	DS-75	DS-150
Opening Method	Bi-parting		Single sliding	
Applicable Door Mass x Door q'ty	75x2	100x2	75x1	100x1
Door area DW XDH (m <sup>2</sup> )	2.6			
Applicable Door Width:DW (mm)	762~1067			
Rate of DH/DW	3.0			
R from door center (mm)	1200R~			
Average speed	0.4m/s or less			
Maximum Operable Wind Speed	100VAC·5A			


### Notice

1. All drawings herein are subject to change without notice.
2. For further details, please contact NABCO sales distributors

Circular Sliding Door  
 Operation Unit "Eu"  
 Installation Drawing of  
 Access Panel Outside type  
 (Elevation)  
 Scale 1:20

参考図書

改訂No.	改訂日時
番号 No.	
1HP102562-01	
<b>Nabtesco</b> Nabtesco Corporation ナブコカンパニー	



Notice

- 1, All drawings herein are subject to change without notice.
- 2, For further details, please contact NABCO sales distributors

Circular Sliding Door  
 Operation Unit "Eu"  
 Installation Drawing of  
 Access Panel Outside type  
 (Section)  
 Scale 1:20

改訂No.	改訂日時
番号 NO.	1HP102562-02
<b>Nabtesco</b> Nabtesco Corporation	

参考図書