

Specification

	Door Operator DS-500	
	Bi-parting	Single sliding
Opening Method	Bi-parting	Single sliding
Applicability		
Applicable Door Mass x Door q'ty	1000x2	2000x1
Door area DW XDH (m²)	27	45
Applicable Door Width:DW (mm)	6100	10100
Applicable Door Height:DH (mm)	4500	
Average speed	~0.3m/sx2	~0.3m/s
Power supply	200VAC·10A	
Maximum Operable Wind Speed	15m/s or less (When door area is within the above applicability)	


Notice

- 1, All drawings herein are subject to change without notice.
- 2, For further details, please contact NABCO sales distributors.

Drawing of DS-500
Reduction gear type (Elevation)
Scale 1:30

改訂No.	改訂日時
番号 NO.	
1HP111397-01	
Nabtesco Nabtesco Corporation	

Access panel side



Notice

- 1, All drawings herein are subject to change without notice.
- 2, For further details, please contact NABCO sales distributors.

Drawing of DS-500
 Reduction gear type
 (Section)
 Scale 1:2

改訂No.	改訂日時
番号 NO.	
1HP111397-02	
 Nabtesco Corporation	

参考図書