





Specification

Opening Method		Single sliding		Bi-parting	
Door Operator		DS-60	DS-75	DS-60	DS-75
Specification		Concealed side mount type for aluminum			
Applicability	Applicable Door Mass x Door q'ty	75kg×1	100kg×1	60kg×2	85kg×2
	Door area DW×DH(㎡)	2.2㎡	2.8㎡	1.8㎡	2.6㎡
	Rate of DH/DW	4.0			
average speed		0.1~0.6m/s		0.1~0.55m/s	
Power supply		100VAC・5A			
Maximum Operable Wind Speed		15m/s or less			

Notice

1、All drawings herein are subject to change without notice.
2、For further details, please contact NABCO sales distributors

Drawing of DS-60/75 for aluminum (Elevation) Scale 1:20

参考図書

改訂No.	改訂日時

番号 NO.
1HP102559-01

Nabtesco
Nabtesco Corporation

NABCO

Access panel side



Notice

1、All drawings herein are subject to change without notice.
2、For further details, please contact NABCO sales distributors.

Drawing of DS-60/75 for aluminum (Section) Scale 1:1

参考図書

1	2008.8.18
改訂No.	改訂日時

番号 NO.
1HP102559-02

Nabtesco
Nabtesco Corporation