


Specification

Item	Standard	Option
Door Material	Aluminum	-
Glass	Insulated glass	-
Glass Thickness	6+12A+6	-
Active sensor	-	Option
Safety beam	-	NP-01/NP-80
Electric lock	-	SKD-C/PL-T10U
Floor lock	-	NDL-12
Program switch	-	Option
Floor track threshold	Exist	Bottom guide
Transom	-	Exist



NAME

NAL-Insulated glass

Bi-part sliding door