



- NOTE**
- Use safety glass.
 - 1. Attach the warning label and automatic door label to the door.
 - 2. Attach more than 1 label to the door at least, positioning center of the label from FL+750mm to 1750mm in height.

Specification

Opening Method	Single Sliding			Bi-parting		
	VS-60	VS-85	VS-150	VS-60	VS-85	VS-150
Door Operator						
Railbase	Type S					
Applicability	Door Weight (kg) x Door q'ty	75 x 1	100 x 1	120 x 1	60 x 2	85 x 2
	Door width : DW (mm)	650-2500				
	Ratio of DH/DW	4 or less				
	Door operation speed (m/s)	0.1 - 0.7				
	Power supply	230VAC±10%, 50/60Hz, 2.5A				
Available ambient conditions	Ambient temperature	-20 to 50°C				
	Ambient humidity	20 to 90% RH (no icing or condensation)				
	Electromagnetic field immunity	Industrial environment (IEC/JIS C 61000-6-2)				

Notice

1. All drawings herein are subject to change without notice.
2. For further details, please contact NABCO sales distributors.

Drawing of V-60/85/150SL-S
Surface mounted type (150 mm surface)
(Elevation)
Scale 1:20

-	-
初版	2019.08.01
改訂No.	改訂日時
番号 No.	1DK202032

