







Power supply not less than 2.5A  
Incl. ground wire into operation case  
(by other)



#### Specification

Item	Standard	Option
Door leaf	Steel (painting)	Aluminum (painting)
Lead Plate	2mm	3mm
Header	Aluminum/Silver	Painting
Three-sided jamb	Aluminum/Silver	Painting
Operator	VS-150	-
Safety beam	NP-01	NP-80
Foot switch	Ft-80	Option
Handle	Recessed handle	Option
Electric lock	-	Option



Door opening width (W)

Remark: It need to adjust the height of waist plate, when opening height is over 2200mm.

NAME \_\_\_\_\_ MD-SX1-SL \_\_\_\_\_  
Left hand sliding door