






Power supply not less than 2.5A
Incl. ground wire into operation case
(by other)




Brand label



Specification

Item	Standard	Option
Door leaf	Steel (painting)	Aluminum (painting)
Lead Plate	3mm	4mm
Header	Aluminum/Silver	Painting
Three-sided jamb	Aluminum/Silver	Painting
Operator	VS-150	-
Safety beam	NP-01	NP-80
Foot switch	Ft-80	Option
Handle	Recessed handle	Option
Electric lock	-	Option

Scope: Maximum weight of door : 350Kg



Remark: It need to adjust the height of waist plate, when opening height is over 2200mm.

NAME _____ MD-SX2-SL
Left hand sliding door