




Power supply not less than 2.5A  
Incl. ground wire into operation case  
(by other)




Access panel side

Left hand



Specification

Item	Standard	Option
Door leaf	Steel (painting)	Aluminum (painting)
Header	Aluminum/Silver	Painting
Three-sided jamb	Aluminum/Silver	Painting
Operator	VS-150	-
Safety beam	NP-01	NP-80
Foot switch	Ft-80	Option
Handle	Recessed handle	Option
Electric lock	-	Option




Access panel side

A-A

Type	Hand	Remark
01	Left	As shown
02	Right	Mirror view

Scope: Maximum weight of door : 150Kg



Remark: It need to adjust the height of waist plate, when opening height is over 2200mm.