








Power supply not less than 2.5A  
Incl. ground wire into operation case  
(by other)



Specification

Item	standard	Option
Door leaf	Aluminum/Silver	Painting
Glass	8mm Tempered glass	8+34+8 Tempered insulated glass with ceramic frit
Header	Aluminum/Silver	Painting
Three-sided jamb	Aluminum/Silver	Painting
Operator	VS-150	-
Safety beam	NP-01	NP-80
Foot switch	Ft-80	Option
Handle	Recessed handle	Option
Electric lock	-	Option



show: the rang of type 03 and type 04

Type	Hand	Option	Remark
01	Left	8mm Tempered glass	As shown
02	Right	8mm Tempered glass	Mirror view
03	Left	8+34+8 Tempered insulated glass	As shown
04	Right	8+34+8 Tempered insulated glass	Mirror view

NAME	NAX-SG-S NAX Hermetic Door
------	-------------------------------