



3x2.5mm<sup>2</sup> (220V, 50HZ+PE, 16A) power cable should be prepared unseenly at the center point A or B for 5 meters.



Standard dimensions

| D    | W<br>(Stainless surface) | W<br>(Painting) | B    | A       | H         |
|------|--------------------------|-----------------|------|---------|-----------|
| 3000 | 3230                     | 3220            | 1988 | 500~600 | 2200~3000 |
| 3200 | 3430                     | 3420            | 2130 |         |           |
| 3400 | 3630                     | 3620            | 2271 |         |           |
| 3600 | 3830                     | 3820            | 2413 |         |           |
| 3800 | 4030                     | 4020            | 2554 |         |           |
| 4000 | 4230                     | 4220            | 2695 |         |           |
| 4200 | 4430                     | 4420            | 2837 |         |           |

NAME

RL-4W 4-wings column revolving door