

Specification


Door Operator	GT-710C	
Opening Method	Single swing (One leaf, 90 degrees)	
Applicability	Applicable Door Mass x Door q'ty	90 x 1
	Door area DW x DH(m ²)	Max 2.6
	Applicable Door Width: DW (mm)	838~1219
	Door thickness (mm)	30~50
Power assist function	When the door is pushed open by hand, then it opens automatically to be fully opened.	
Operation At Power Failure	Manual open and automatic close	
Operator Dimension	W880 x H158 x D147	
Operator Box Color	silver or Bronze	
Average speed	~35°/s	
Power supply	100VAC-5A	

Notice

- All drawings herein are subject to change without notice.
- For further details, please contact NABCO sales distributors

Drawing of GT-710C Power Assist Door (Elevation) Scale 1 : 20

2	2017. 4. 26
1	2016. 12. 1
Rev No.	Date of Rev
NO.	
1DK123841	




Notice

- 1、 All drawings herein are subject to change without notice.
- 2、 For further details, please contact NABCO sales distributors

**Drawing of GT-710C
Power Assist Door out swing
(Section)
Scale 1 : 2**

2	2017. 4. 26
1	2016. 12. 1
Rev No.	Date of Rev
NO.	1DK123841



Notice

- 1、 All drawings herein are subject to change without notice.
- 2、 For further details, please contact NABCO sales distributors

Drawing of GT-710C Power Assist Door in swing (Section) Scale 1 : 2

2	2017. 4. 26
1	2016. 12. 1
Rev No.	Date of Rev
NO.	1DK123841