



3x2.5mm<sup>2</sup> (220V, 50HZ+PE, 16A) power cable should be prepared unseenly at the center point A or B for 5 meters.

If fire control is needed, please provide a set of two core cables (value of resistance is below 5 Ohm

and passive normally open signal) unseenly at the center point A or B for 5 meters.



ELEVATION



PLAN

Standard dimensions

D	W (Painting)	W (Stainless surface)	C	B	A	H
2800	3020	3030	1242	1238	300~600	2200~3000
3000	3220	3230	1342	1338		
3200	3420	3430	1442	1438		
3400	3620	3630	1542	1538		
3600	3820	3830	1642	1638		
3800	4020	4030	1742	1738		
4000	4220	4230	1842	1838		
4200	4420	4430	1942	1938		
4400	4620	4630	2042	2038		
4600	4820	4830	2142	2138		
4800	5020	5030	2242	2238		

NAME

CS2A 2-wings show box revolving Door