



3x2.5mm² (220V, 50HZ+PE, 16A) power cable should be prepared unseenly at the center point A or B for 5 meters.
If fire control is needed, please provide a set of two core cables (value of resistance is below 5 0hm and passive normally open signal) unseenly at the center point A or B for 5 meters.



Standard dimensions

D	W (Painting)	W (Stainless surface)	C	B	A	H
3600	3820	3830	646	1624	550~600	2200~3000
3800	4020	4030	696	1724		
4000	4220	4230	746	1824		
4200	4420	4430	796	1924		
4400	4620	4630	846	2024		
4600	4820	4830	896	2124		
4800	5020	5030	946	2224		

NAME

CS2A-W 2-wings column revolving door