




Exterior side



Specification

| Item | Standard | Option |
|-----------------------|----------------|-----------------|
| Door material | Aluminum | - |
| Glass | Tempered glass | Laminated glass |
| Glass thickness | 10mm/12mm | ≤12mm |
| Jamb tube size | 44mm*114mm | 51mm*178mm |
| Active sensor | NH-203 | Option |
| Safety beam | NP-01 | - |
| Electric lock | - | Option |
| Floor lock | - | Option |
| Program switch | - | Option |
| Floor track threshold | Full length | Half length |
| Transom | - | Exist |



Notes:
1. The bottom support wheel is required when the sliding door than 1100mm or the door is larger than 90kg.

| No. | Standard Size | | | | |
|-----|---------------|--------------|-----------------------|--------------|----------|
| | Door width | Door opening | Full breakout opening | Sliding door | Sidelite |
| 01 | 3000 | 1278.5 | 2691 | 720 | 755 |
| 02 | 3500 | 1528.5 | 3191 | 845 | 880 |
| 03 | 4000 | 1778.5 | 3691 | 970 | 1005 |

NAME

GT-1175B0-F0-SLM
Bi-part No transom