



Exterior elevation
1:30




Plan

Access cover side(Interior)




Horizontal section
1:8

Exterior side



A-A Vertical section
1:8


Interior side



Brand label

Specification

Item	Standard	Option
Door material	Aluminum	-
Glass	Tempered glass	Laminated glass
Glass thickness	10mm/12mm	≤12mm
Jamb tube size	44mm*114mm	51mm*178mm
Active sensor	NH-203	Option
Safety beam	NP-01	-
Electric lock	-	Option
Floor lock	-	Option
Program switch	-	Option
Floor track threshold	Full length	Half length
Transom	-	Exist



Notes:

1. The bottom support wheel is required when the sliding door is wider than 1100mm or the door is larger than 90kg.

NO.	标准尺寸				
	Door width	Door opening	Full breakout opening	Sliding door	Sidelite
01	2000	922	1801	946.5	983.5
02	2400	1122	2201	1146.5	1183.5

NAME

GT-1175B0-F0-SLM

Right hand No transom