



Horizontal section
1:8

Exterior side




A-A Vertical section
1:8



Brand Label

Specification

Item	Standard	Option
Door material	Aluminum	-
Glass	Tempered glass	Laminated glass
Glass thickness	10mm/12mm	≤12mm
Jamb tube size	44mm*114mm	51mm*178mm
Active sensor	NH-203	Option
Safety beam	NP-01	-
Electric lock	-	Option
Floor lock	-	Option
Program switch	-	Option
Floor track threshold	Full length	Half length
Transom	Exist	-



Notes:
1. The bottom support wheel is required when the sliding door is wider than 1100mm or the door is larger than 90kg.

No.	Standard size				
	Door width	Door opening	Full breakout opening	Sliding door	Sidelite
01	3000	1278.5	2691	720	755
02	3500	1528.5	3191	845	880
03	4000	1778.5	3691	970	1005

NAME

GT-1175B0-F0-SLM

Bi-part Transom