





Access cover side (Interior)



Brand label

Specification

Item	Standard	Option
Door material	Aluminum	-
Glass	Tempered Glass	Insulated glass /Laminated glass
Glass thickness	10mm/12mm	≤25mm/≤12mm
Active sensor	NH-203	Option
Safety beam	NP-01	NP-80
Electric lock	-	Option
Mechanical lock	Manual lock	-
Program switch	-	Option
Floor track threshold	Half length	Full length
Transom	-	Exist



Notes:

1. The bottom support wheel is required when the sliding door is wider than 1370mm or the door is larger than 90kg.
2. A Muntin Bar is required when the sliding door is wider than 1500mm.

NO.	Standard Size				
	Door width	Door opening	Full breakout opening	Sliding door	Sidelite
01	2000	829	1797	1013	951
02	2500	1079	2297	1263	1201

NAME

GT-1175B0-F0

Right hand No transom Standard jamb