


# Specification

Item	Standard	Option
Door material	Aluminum	-
Glass	Tempered glass	Insulated glass /Laminated glass
Glass thickness	10mm/12mm	≤25mm/≤12mm
Active sensor	NH-203	Option
Safety beam	NP-01	NP-80
Electric lock	-	Option
Mechanical lock	Manual lock	-
Program switch	-	Option
Floor track threshold	Half length	Full length
Transom	Exist	-



- Notes:
1. The bottom support wheel is required when the sliding door is wider than 1370mm or the door is larger than 90kg.
  2. A Muntin Bar is required when the sliding door is wider than 1500mm.

NO.	Standard size				
	Door width	Door opening	Full breakout opening	Sliding door	Sidelite
01	3000	1203	2682	785	723
02	3500	1453	3182	910	848
03	4000	1703	3682	1035	973
04	4500	1953	4182	1160	1098
05	5000	2203	4682	1285	1223

NAME GT-1175B0-F0  
Bi-part Transom Standard jamb