


Specification

Item	Standard	Option
Door material	Aluminum	-
Glass	Tempered glass	Insulated glass /Laminated glass
Glass thickness	10mm/12mm	≤25mm/≤12mm
Active sensor	NH-203	Option
Safety beam	NP-01	NP-80
Electric lock	-	Option
Mechanical lock	Manual lock	-
Program switch	-	Option
Floor track threshold	Full length	-
Transom	Exist	-



Remark:

1. The range is only base on 10mm glass.
2. The bottom support wheel is required when the door is larger than 90kg.

No.	Standard size				
	Door width	Door opening	Full breakout opening	Sliding door	Sidelite
1	4000	2192	3500	705	649
2	4500	2525	4000	789	733
3	5000	2858	4500	872	816

NAME

GT-1175B0-TP
Bi-part Transom