



Power supply not less than 2.5A Incl. ground wire into operation case (by other)
--




Exterior elevation
1:30




Plan


Access cover side(Interior)




B--B Horizontal section
1:8



A-A Vertical section
1:8



Brand label



Door width (W0)

Notes:

1. The bottom support wheel is required when the sliding door is wider than 1370mm or the door is larger than 90kg.
2. A Muntin Bar is required when the sliding door is wider than 1500mm.

Specification

Item	Standard	Option
Door material	Aluminum	-
Glass	Tempered glass	Insulated glass /Laminated glass
Glass thickness	10mm/12mm	≤25mm/≤12mm
Active sensor	NH-203	Option
Safety beam	NP-01	NP-80
Electric lock	-	Option
Mechanical lock	Manual lock	-
Program switch	-	Option
Floor track threshold	Half length	Full length
Transom	Exist	-

NO.	Standard Size				
	Door width	Door opening	Full breakout opening	Sliding door	Sidelite
01	2000	829	1797	1013	951
02	2500	1079	2297	1263	1201

NAME	GT-1175B0-F0
	Right hand Transom Standard jamb